

Model No	Maximum Spacing (Ft)			
	Ceilings up to 9m (30 ft)		Ceilings above 9m (30 ft)	
	Smooth Ceiling	to Wall or Partition	Smooth Ceiling	to Wall or Partition
LHD-68-P	35	17.5	17.5	8.75
LHD-88-P	35	17.5	17.5	8.75
LHD-105-P	35	17.5	17.5	8.75
LHD-68-N	15	7.5	7.5	3.75
LHD-88-N	15	7.5	7.5	3.75
LHD-105-N	15	7.5	7.5	3.75
LHD-185-N	-	-	-	-

* The LHD cable should be installed with a minimum distance between the cable and the ceiling of 20mm to allow hot gases rising from an event to trigger the detection cable

* LHD-185-N used for special applications only and so no spacing provided

Illustration: LHD-68-P (Ceiling height less than 9m)

